



Item number 23.0290-*

Insulated, with \emptyset 2 mm rigid socket and insulated head undetachable. With \emptyset 2 mm cross hole for quick wire connection. Machined brass. For mounting, with anti-rotation lug, in front panels up to 4 mm thick. Threaded bolt M3.

| Technical data | |
|--------------------------------------|-------------------------|
| Diameter of plug system | 2 mm |
| Rated Values | 30 V, 15 A / 60 V, 15 A |
| Surface treatment electrical contact | Ni |
| Base material electrical contact | CuZn |
| Standard color(s) * | 21 22 |
| Thread | M3 |
| Test accessory acc. to | IEC EN 61010-2-030 |