







Item number 64.9289- \*\*

Highly flexible, with in-line  $\varnothing$  4 mm MULTILAM plugs on both ends.

Technical data	
Diameter of plug system	4 mm
Rated Values	30 V, 15 A / 60 V, 15 A
Surface treatment electrical contact	Ni
Base material electrical contact	CuZn
Standard color(s) *	21 22 23 24 25
Lead lengths	100; 200 cm
Lead insulation	PVC
Lead cross section	0,75 mm²
Test accessory acc. to	IEC EN 61010-031