





Item number 66.9394- 2*

Highly flexible, with in-line Ø 4 mm MULTILAM plug with rigid insulating sleeve on both ends.Test lead with integrated high breaking capacity fuses designed for 1000 V, CAT IV in accordance with IEC/EN 61010-031 and allow for the use of Ø 4 mm safety probes and test clips for fuse-protected d measurements. The two-part fused connector can be easily unscrewed and accepts a high breaking capacity fuse measuring 6.3 x 32 mm. The fuse is not supplied.

Technical data Diameter of plug system 4 mm 1000 V, CAT IV, 8 A **Rated Values** Surface treatment electrical contact Ni CuZn Base material electrical contact Standard color(s) * **21 22 23 24 25 26 27 28** Optional color(s) 29 100; 150; 200 cm Lead lengths PVC Lead insulation Lead cross section 1.0 mm² Test accessory acc. to IEC EN 61010-031 User-Information I 091 Accessories: High breaking capacity fuse DMI-0,5A; High breaking Remarks capacity fuse DMI-1,6 A Approvals UL, CE

Staubli is a trademark of Stäubli International AG, registered in Switzerland and other countries. We reserve the right to modify product specifications without prior notice. © Stäubli 2022 | ec.marcom@staubli.com | Photo credits: Stäubli | www.staubli.com