


FLEXI-2V 0,75





Item number 60.7028-*

Highly flexible stranded wire 0,75 mm² with reinforced, double-layer insulation for the highest safety

Technical data	
Rated Values	AC 1000 V, 15 A / DC 1500 V, 15 A
Standard color(s) *	21 22 23
Lead insulation	PVC
Temperature range	-10 °C +70 °C
Strand design (n x Ø mm)	196 x 0,07
Lead weigth	18.0 kg/km
Conductor diameter	1.25 mm
Cable diameter	3.5 mm
Insulation thickness	1.1 mm
Approvals	UR, CE, UKCA, EAC