


FLEXI-1V 1,5



Item number 60.7088-*

Highly flexible stranded wire 1,5 mm² with reinforced insulation.

Technical data	
Rated Values	AC 1000 V, 24 A / DC 1500 V, 24 A
Standard color(s) *	20 21 22
Lead insulation	PVC
Temperature range	-10 °C ... +70 °C
Strand design (n x Ø mm)	392 x 0,07
Lead weighth	27.0 kg/km
Conductor diameter	1.7 mm
Cable diameter	3.9 mm
Insulation thickness	1.1 mm
Approvals	UR, CE, UKCA, EAC