



FLEXI-S/POAG-HK6



Item number 15.2015-*

Highly flexible, reinforced insulated stranded wire 6,0 mm².

Technical data	
Rated Values	AC 600 V, 54 A
Standard color(s) *	20
Lead insulation	PVC
Temperature range	-10 °C ... +70 °C
Strand design (n x Ø mm)	1548 x 0,07
Lead weight	80.0 kg/km
Conductor diameter	3.7 mm
Cable diameter	5.9 mm
Insulation thickness	1.1 mm